

MONTAGEANLEITUNG

 MONTAGEANLEITUNG
 ASSEMBLY INSTRUCTION
 DE INSTRUCTIE VAN DE ASSEMBLAGE
 ISTRUZIONI DI MONTAGGIO
 INSTRUCCIÓN ENSAMBLAJE
 INSTRUCTION DE MONTAGE
 NÁVOD K MONTÁŽI
 MONTERINGSANVISNING

 MONTAJ TALIMATI
 ASENNUSOHJE
 BRUGSANVISNING
 BRUKSANVISNING
 UPUTE ZA MONTAŽU
 NAVODILA ZA MONTAŽU
 SZERELÉSI ÚTMUTATÓ
 INSTRUCTIUNI DE MONTAJ



Version 16.6

Modell-Nr.

70390

Friedrich Küpper GmbH
 Friedrich-Küpper-Weg
 54570 Berlingen
 Deutschland

Telefon +49 (0) 65 91 - 95 42 0
 Telefax +49 (0) 65 91 - 95 42 17
 E-Mail info@friedrich-kuepper.de
 Internet www.friedrich-kuepper.de

ART.-NR.	FRONT	KORPUS
70391	Dunkelrot NCS S 1580-R	Hellgrau PANTONE Cool Gray 11 C
70392	Rot* ähnl. RAL 3002	Silber*
70393	Dunkelblau PANTONE 2379 C	Hellgrau PANTONE Cool Gray 11 C
70394	Silber Metallic NCS S 4005-B	Hellgrau PANTONE Cool Gray 11 C
70396	Silber*	Schwarz* RAL 9005
70397	Ultramarinblau* RAL 5002	Silber*
70398	Anthrazitgrau RAL 7016	Hellgrau PANTONE Cool Gray 11 C
70399	Schwarz Struktur RAL 9005	Hellgrau PANTONE Cool Gray 11 C

* Auslauffarbe/ discontinued color

EINZELTEILE / PIECES

1× **A**

450 mm × 450 mm

Art.-Nr. E0030 (Silber/silver)

Art.-Nr. E0031 (Schwarz/black)

Art.-Nr. E4056 (Hellgrau/light grey)




1× **G**

1770 mm × 385 mm

Art.-Nr. E0052 (Silber/silver)

Art.-Nr. E0053 (Schwarz/black)

Art.-Nr. E4057 (Hellgrau/light grey)



2× **E**

1770 mm × 430 mm

Art.-Nr. E0043 (Silber/silver)

Art.-Nr. E0108 (Schwarz/black)

Art.-Nr. E4059 (Hellgrau/light grey)




1× **J**

450 mm × 100 mm

Art.-Nr. E0066 (Silber/silver)

Art.-Nr. E0067 (Schwarz/black)

Art.-Nr. E4058 (Hellgrau/light grey)



1× **C**

450 mm × 405 mm

Art.-Nr. E0039 (verzinkt/galvanised)



1× **L**

1665 mm × 450 mm

Art.-Nr. E0078 (Silber/silver)

Art.-Nr. E0075 (Rot/red)

Art.-Nr. E0077 (Blau/blue)

Art.-Nr. E8112 (Dunkelrot/dark red)

Art.-Nr. E8312 (Dunkelblau/dark blue)

Art.-Nr. E8412 (Silber metallic/silver metallic)

Art.-Nr. E8812 (Anthrazitgrau/anthracite grey)

Art.-Nr. E8912 (Schwarz Struktur/black)




4× **N**

450 mm × 380 mm

Art.-Nr. E0100 (verzinkt/galvanised)



BEUTELINHALT / BAG CONTENT

 4× M6 × 16 mm Art.-Nr. E0750	 10× M6 × 12 mm Art.-Nr. E0751	 4× M6 × 16 mm Art.-Nr. E0752	 18× ø 6,4 mm Art.-Nr. E0753	 18× M6 Art.-Nr. E0754	 2× M4 × 10 mm Art.-Nr. E0755
 2× M4 Art.-Nr. E0290	 2× ø 4,3 mm Art.-Nr. E0757	 2× 5 × 5 Art.-Nr. E0759	 2× 5 × 15 Art.-Nr. E0760	 4× Art.-Nr. E0758	 4× Art.-Nr. E0761
 4× Art.-Nr. E0762	 2× Art.-Nr. E0763	 2× Art.-Nr. E0764	 1× Art.-Nr. E0766	 1× Art.-Nr. E0768	 1× Art.-Nr. E0770
 1× Art.-Nr. E0771	 1× Art.-Nr. E0772	 1× Art.-Nr. E0773			

BENÖTIGTES WERKZEUG / NEEDED TOOLS


1  PH 1 × 100 PH 2 × 100 Schlitz 6,5 × 150	2  SW 7 SW 10	3  6 mm
4 	5 	6  5 mm
9 		

1.

① 
Schlitz 6,5 x 150



2.



3.



2× M6



2× M6 × 12



2× 6,4 MM

②



SW10



4.



2× M6



2× M6 × 12



2× 6,4 MM

②



SW10



5.



2×



6.



4× M6



4× M6 × 16



4× 6,4 mm




2×



PH 2 × 100



SW10



7.  2x



8.  4x M6 x 16



9.  4x M6  4x 6,4 mm

⑥ 




10.  4x



11.  2x

①  PH 2x100



12.



13.

4x M6 4x M6 x 12 4x 6,4 MM


② SW10



14.

2x M6 2x M6 x 12 2x 6,4 MM

② SW10



15.

①
PH 2x100



16.



17.




18.  2x 5x15

⑤ 



19.  2x 5x5



20.  1x



21.

1x M4

1x M4x10

1x 4,2mm

① PH 1x100

② SW 7



22.



23.

1x


1x M4

1x M4x10

1x 4,2mm

① PH 1x100

② SW 7



24.

1x

1x

1x

⑨



25. 1x _____




26. 1x _____



27. 1x 1x 1x

⑨ 





Modell-Nr.

70390