

MONTAGEANLEITUNG

-  MONTAGEANLEITUNG
-  ASSEMBLY INSTRUCTION
-  DE INSTRUCTIE VAN DE ASSEMBLAGE
-  ISTRUZIONI DI MONTAGGIO
-  INSTRUCCIÓN ENSAMBLAJE
-  INSTRUCTION DE MONTAGE
-  NÁVOD K MONTÁŽI
-  MONTERINGSANVISNING

-  MONTAJ TALIMATI
-  ASENNUSOHJE
-  BRUGSANVISNING
-  BRUKSANVISNING
-  UPUTE ZA MONTAŽU
-  NAVODILA ZA MONTAŽO
-  SZERELÉSI ÚTMUTATÓ
-  INSTRUCTIUNI DE MONTAJ



Version 16.6

Modell-Nr.

89200/89300

Friedrich Küpper
Friedrich-Küpper-Weg
54570 Berlingen
Deutschland

Telefon +49 (0) 65 91 - 95 42 0
Telefax +49 (0) 65 91 - 95 42 17
E-Mail info@friedrich-kuepper.de
Internet www.friedrich-kuepper.de

EINZELTEILE / PIECES

1× **A**



527 mm × 905 mm (mit/with Logo Küpper)

Art.-Nr. E0752 (Silber/silver)

Art.-Nr. E1133 (Schwarz/black)

Art.-Nr. E4052 (Hellgrau/light grey)

Art.-Nr. E8962 (Schwarz Struktur/black structure)

4× **A**

(nur/only Art. 89200)

5× **A**

(nur/only Art. 89300)



527 mm × 905 mm

Art.-Nr. E0752 (Silber/silver)

Art.-Nr. E1133 (Schwarz/black)

Art.-Nr. E4052 (Hellgrau/light grey)

Art.-Nr. E8962 (Schwarz Struktur/black structure)

1× **C**



828 mm × 430 mm

Art.-Nr. E1134 (Silber/silver)


Art.-Nr. E1135 (Schwarz/black)

Art.-Nr. E4053 (Hellgrau/light grey)

Art.-Nr. E8963 (Schwarz Struktur/black structure)

2× **B**

Art. 89200



1800 mm × 530 mm

Art.-Nr. E1131 (Silber/silver)

Art.-Nr. E1132 (Schwarz/black)


Art.-Nr. E4054 (Hellgrau/light grey)

Art.-Nr. E8964 (Schwarz Struktur/black structure)

**Nur bei Art.89200 im Lieferumfang
Only at 89200 included**

2× **G**

Art. 89300



2000mm × 530 mm

Art.-Nr. E1136 (Silber/silver)


Art.-Nr. E1137 (Schwarz/black)

Art.-Nr. E4055 (Hellgrau/light grey)



Art.-Nr. E8965 (Schwarz Struktur/black structure)

**Nur bei Art.89300 im Lieferumfang
Only at 89300 included**

BEUTELINHALT / BAG CONTENT

 26× (89200) 30× (89300) M5 × 10 mm Art.-Nr. E0286	 26× (89200) 30× (89300) ø 5,3 mm Art.-Nr. E0287	 26× (89200) 30× (89300) M5 Art.-Nr. E0288	 4× Art.-Nr. E0294	 4× Art.-Nr. E0293	 4× M8 Art.-Nr. E0295
 2× E6 × 30 mm Art.-Nr. E0375	 2× 15 × 15 mm Art.-Nr. E0376	 2× 4,5 × 60 mm Art.-Nr. E0374			

BENÖTIGTES WERKZEUG / NEEDED TOOLS

1  PH 2 × 100	2  SW 8	3 
4  6 mm	5 	6 
7 		


1a.

4x M8

4x

4x

3



B



1b.



2a.

10× M5 10× M5×10 10× Ø 5,3mm


②  SW8 ①  PH2×100




2b.



2c.



2d.



3.



10× M5



10× M5×10



10× Ø 5,3 mm

②



SW8

①




PH2×100



Befestigen Sie das Stützblech (C) auf der Rückseite mit je 6 x E0286/E0287/E0288
Fix the support plate (C) on the back side with each 6x E0286/E0287/E0288



A.




B.



C.



D.



Modell-Nr.

893000/89200